


**PRIMASONICS® AUDIOSONIC™ ACOUSTIC CLEANER
GENERAL PIPING ARRANGEMENT
(PRIMASONICS PART NUMBER IN BRACKETS)**

AIR PRESSURE REQUIREMENT
4.8-6.2 bar 70-90 psi 480-620 kPa
AIR CONSUMPTION
1130-2260 l/min 40-80 SCFM when sounding



- (A) EITHER FITTED WITH AN INDIVIDUAL TIMER OR OPERATED VIA PLC (MULTI INSTALLATION)
- (B) OPTIONAL BUT ADVISED IN REMOTE INSTALLATIONS
- (C) OPTIONAL BUT ADVISED IF AIR QUALITY OR PRESSURE IS SUSPECT
- (D) MAXIMUM ADVISED LENGTH 4M, PREFERRED 2M
- (E) OPTIONAL BUT REQUIRED IF NO PLC CONTROL
- (F) OPTIONAL BUT ADVISED TO ISOLATE COMPRESSED AIR

DRAWING N° PAS-G001

Safe, automated, effective prevention and removal of dry powder, particulate build-up and blockages